

# PHILIPS

Reflector 90W  
PAR38 E26 x2

LED

2700/3000/3500/4000/5000  
K

900lm

25000h

Dimming

046677586478



## Creative innovation to realize color selection to match your desired atmosphere

Philips LED spots provide an easy solution to realize the color selection to fit for your desired application. This spot provided a flood beam, it's perfect for accent lighting. It's dimmable, with exceptionally long life, and significant energy savings.

### Create the right light for your home

- Perfect for accent lighting

### Light beyond illumination

- Instant on

# Highlights

## 40° deg beam – flood [LED lamps]

An LED flood with a wide-angle light output (40 degrees), suitable for both

accent lighting and general purpose lighting.

**Instant on**

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Type of glass: Clear
- Bulb Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb Material: Plastic

## Bulb dimensions

- Height: 12.9 cm
- Width: 12.3 cm

## Design and finishing

- Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700/3000/3500/4000/5000 K
- Nominal luminous flux: 900 lm

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Efficacy: 90 lm/W

## Packaging information

- EAN: 046677586478
- EOC: 586479
- Product title: 10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 10 W
- Wattage equivalent: 90 W

## Product dimensions and weight

- Length: 12.9 cm

## Rated values

- Rated peak intensity: 1533 cd

## Technical specifications

- Frequency: 60 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 046677586478
- Net weight: 0.28 kg
- Gross weight: 0.42 kg
- Height: 18 cm
- Length: 13.1 cm
- Width: 23.6 cm
- Material number (12NC): 929003741003



Issue date: 2024-07-25  
Version: 0.99

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)