

# PHILIPS

Filament Bulb Clear  
60W A19 E26

LED

2700K

800lm

15000h

046677586898



## Dusk to Dawn

Philips LED Dusk to Dawn bulb is designed to save even more energy than regular LED by turning itself on and off with the level of daylight - providing secure light during the night, and turning off with the light of day

### Light beyond illumination

- Built-in automatic on/off light sensor

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Clear
- Dimmable: No
- Bulb Material: Glass

## Bulb dimensions

- Height: 10.5 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 306 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 800 lm

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 111 lm/W

## Packaging information

- EAN: 046677586898
- EOC: 586891
- Product title:  
7A19/D2D/927/CL/G/E26/ND T20  
3/1PF

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 7.2 W
- Wattage equivalent: 60 W

## Product dimensions and weight

- Length: 10.5 cm

## Technical specifications

- Frequency: 50-60 Hz

046677586898

**Packaging dimensions and weight**

- EAN/UPC - product: 046677586898
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 17.2 cm
- Length: 6.6 cm
- Width: 7.6 cm
- Material number (12NC): 929003744793



Issue date: 2024-06-19  
Version: 0.115

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)