

# PHILIPS

6 inch Recessed Light  
Recessed light 12W

Recessed Lights

2700-3000-3500-4000-5000  
K

White

Dimmable;Water Resistant



046677588083



## High quality LED light designed to last for years

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

### High quality light

- EyeComfort – light that's easy on your eyes

# Highlights

## EyeComfort – light that's easy on your eyes



Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable

light, but also stays that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal

## Durability

- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: 4 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bathroom, Bedroom, Dining Room, Hallway, Home Office, Kitchen, Living Room
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, Water Resistant

## Other characteristics

- Lamp current: 100 mA
- Efficacy: 83 lm/W

## Power consumption

- Power factor: 0.9
- Wattage: 12 W

## Product dimensions and weight

- Net weight: 0.39 kg
- Cut out length: 15.5 cm
- Cut out width: 15.5 cm
- Height: 3 cm
- Recessed distance: 0 cm

## Service

- Warranty: 3 year(s)

#### Technical specifications

- Lifetime up to: 50,000 hour(s)
- Diameter: 170 mm
- Total lumen output fixture: 1000
- Light color:  
2700/3000/3500/4000/5000
- Mains power: AC 120
- Fixture dimmable: Yes
- LED: Yes
- IP code: UL03 - Wet Location (North America)

- Class of protection: UL earthed
- UL Wet/ damp/ dry location: Wet location

#### Packaging dimensions and weight

- EAN/UPC - product: 046677588083
- Net weight: 4.68 kg
- Gross weight: 4.94 kg
- Height: 21.5 cm
- Length: 36 cm
- Width: 18.5 cm



Issue date: 2025-02-11  
Version: 0.119

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.