

# PHILIPS

Filament Candle Clear  
40W B11 E26 x3

LED

5000K

300lm

15000h

Dimming

046677588564



## Bright LED lighting with excellent light quality

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E26) fittings.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: B11
- Socket: E26
- Bulb Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb Material: Glass

## Bulb dimensions

- Height: 9 cm
- Width: 3.5 cm

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 5000 K
- Nominal luminous flux: 300 lm

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 85 lm/W

## Packaging information

- EAN: 046677588564
- EOC: 588566
- Product title: 3.5B11/PER/UD50/CL/G/E26/D/T20 3/3PF

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 3.5 W
- Wattage equivalent: 40 W

## Product dimensions and weight

- Length: 9 cm

## Technical specifications

- Frequency: 60 Hz

046677588564

**Packaging dimensions and weight**

- EAN/UPC - product: 046677588564
- Net weight: 0.05 kg
- Gross weight: 0.1 kg
- Height: 17.1 cm
- Length: 4.6 cm
- Width: 13 cm
- Material number (12NC): 929003090003



Issue date: 2024-09-17  
Version: 0.115

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)