

PHILIPS

Filament Bulb Pink
25W G93 E27

LED

1800K


250lm

15000h

Dimming



8719514269552



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Light beyond illumination

- Vintage style, modern LED technology

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Vintage style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off. "

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Dimmable: Yes
- Bulb Finish: Pink
- Bulb Material: Glass

Bulb dimensions

- Height: 14 cm
- Width: 9.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 1800 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 818 | CCT of 1800K
- Correlated Color Temperature (Nom): 1800 K
- Luminous Flux: 250 lm
- Stroboscopic effect visibility measure (SVM): 0.4
- Luminous Efficacy (rated) (Nom): 55.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, Decorative

Other characteristics

- Efficacy: 55 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514269552
- EOC: 871951426955200
- Product title: LED classic 25W G93 E27 pink D 1PF/4

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 4.5 W
- Wattage equivalent: 25 W
- Power Consumption: 4.5 W

Product dimensions and weight

- Length: 14 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Flickering value (PstLM) – Flickering value as per EN 61000-3-3: 1
- Line Frequency: 50 to 60 Hz
- Dimmable: Yes
- Cap-Base: E27

Packaging dimensions and weight

- EAN/UPC – product: 8719514269552
- Net weight: 0.06 kg
- Gross weight: 0.11 kg
- Height: 18.2 cm
- Length: 10.2 cm
- Width: 13 cm
- Material number (12NC): 929002453801



Issue date: 2024-07-25
Version: 0.180

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com