

PHILIPS

Filament Candle
Clear 40W P45 E27

LED

2200-2700K


470lm

15000h

Dimming



8719514324411



Experience dimmable, warm white LED light

Philips LED clear lustres provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for decorative fixtures with large (E27) fittings.

Choose for a sustainable solution

- Saves up to 90% Energy

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Perfect for decorative fixture



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips, and post lights.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E27
- Bulb Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb Material: Glass

Bulb dimensions

- Height: 7.8 cm
- Width: 4.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2200-2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: instant full light
- Color Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Other characteristics

- Efficacy: 138 lm/W

Packaging information

- EAN: 8719514324411
- EOC: 871951432441100
- Product title: LED classic 40W P45 E27 CL WGD90 SRT4

Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 3.4 W
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): D

8719514324411

Product dimensions and weight

- Length: 7.8 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1109145

Packaging dimensions and weight

- EAN/UPC - product: 8719514324411
- Net weight: 0.02 kg
- Gross weight: 0.04 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-03-09
Version: 0.433

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com