

PHILIPS

Filament Bulb Amber
50W G120 E27

LED

2200K


640lm

15000h

Dimming



8719514337831



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

Dimmable extra warm white light


- Offering cozy and warm ambiance in your room with extra warm white lights, which can dim to create your private atmosphere.

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Dimmable extra warm white light



Enhance the ambiance in your home with extra warm white light that dims smoothly via app or voice to your desired brightness level.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Dimmable: Only with specific dimmers
- Bulb Material: Glass

Bulb dimensions

- Height: 17.8 cm
- Width: 12.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2200 K
- Nominal luminous flux: 640 lm
- Warm-up time to 60% light: instant full light
- Color Code: 822 | CCT of 2200K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, Decorative

Other characteristics

- Efficacy: 87 lm/W

Packaging information

- EAN: 8719514337831
- EOC: 871951433783100
- Product title: LEDCLA 50W G120 E27 922 GOLD SP 1PF/4

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 7.3 W
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): F

Product dimensions and weight

- Length: 17.8 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 574381

Packaging dimensions and weight

- EAN/UPC – product: 8719514337831
- Net weight: 0.1 kg
- Gross weight: 0.2 kg
- Height: 22.6 cm
- Length: 13 cm
- Width: 13 cm
- Material number (12NC):
929003061868



Issue date: 2024-07-25
Version: 0.300

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com