

PHILIPS

Utrecht Post Light
20W E27 No-bulb

Outdoor luminaires

No bulb

Antracite

Water Resistant

8719514417557



Enjoy a lovely garden with light

This Philips Utrecht outdoor post in antracite has an elegant design made of stainless steel. It creates a diffused glow for your garden, and brings social areas to sparkling life with its high quality light.

Ease of use

- No bulb included

Bring design into your garden

- Choose for outdoor pedestal lights

Premium quality

- High quality stainless steel and superior synthetics

Designed for outdoors

- IP44 - weather proof

Highlights

No bulb included

This luminaire comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long lasting light output.

Choose for outdoor pedestal lights

Make the most of your outdoor space with this pedestal light, perfect to light your garden, the edge of your terrace or to accentuate driveways and paths.

High quality stainless steel and superior synthetics

This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality stainless steel and superior synthetics.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Specifications

Design and finishing

- Color: Anthracite
- Material: Stainless Steel

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable height: No
- Adjustable spot head: No
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- click!FIX mounting: Yes
- Day-and-night sensor: No
- Defined light beams: No
- Dimmable: No
- Dimmable with remote control: No
- FFP - Frustration Free Pack: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion & day-and-night sensor: No
- Motion sensor: No
- Perfectly suited for ambiance creation: No
- Perfectly suited for horizontal/vertical mounting: Yes
- Perfectly suited for orientation lighting: No
- Perfectly suited for up/down mounting: No
- Perfectly suited for wall and ceiling installation: No
- Pivotal head (left-right): No
- Portable: No
- Power adapter included: No
- Protection sleeve included: No
- Remote control included: No
- Resistant high quality material: Yes
- Rotates freely in any direction: No
- Solar Energy: No
- Tilttable head (up-down): No
- UK-plug included: No
- USB charging: No
- Warm White Light: No
- Waterproof: Yes
- Centerpiece: No
- Centerpiece: No

Garden area

- Garden area: Garden & Patio

Light characteristics

- Color rendering index (CRI): 0

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Post Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.76 kg
- Height: 80 cm
- Length: 12 cm
- Width: 12 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 0 hour(s)
- Total lumen output fixture: 0
- Light color: 2700
- LED: No
- Fitting/cap: E27
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: Yes

Packaging dimensions and weight

- EAN/UPC - product: 8719514417557
- Net weight: 0.76 kg
- Gross weight: 0.93 kg
- Height: 81 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2024-11-22
Version: 0.393

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com