

# PHILIPS

Shroud Wall Light  
2.3W

Outdoor luminaires

2700K

Black

Sensor;Solar;Water Resistant



8720169265509



## Long-lasting solar-powered garden light for all seasons

Philips Shroud wall light is a reliable solar light that lasts longer time, reduces energy consumption and supports sustainability.

### Easy installation

- No wiring required

### Sustainable light solutions

- Long lifetime up to 15,000 hours

### Advanced LED light

- High quality LED light

### Designed for outdoors

- IP44 - weather proof

### Special characteristics

- Motion sensor, for convenience and reassurance

# Highlights

## No wiring required

This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

## Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

## High quality LED light

These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colors in your garden.

## IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

## Motion sensor, for convenience and reassurance



A motion sensor is included to welcome you when you return home or let you know when someone's on their way.

# Specifications

## Design and finishing

- Color: Black
- Material: Plastic

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Adjustable spot head: No
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Diffused light effect: Yes
- Fully weatherproof: Yes
- Motion sensor: Yes
- Premium quality material: Yes
- Solar Energy: Yes
- Warm glow dimmable light: No
- Warm White Light: Yes
- Centerpiece: No

## Garden area

- Garden area: Garden & Patio

## Light characteristics

- Color rendering index (CRI): 80

**Miscellaneous**

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Sensor, Solar, Water Resistant

**Product dimensions and weight**

- Net weight: 0.378 kg
- Height: 18.8 cm
- Length: 11.4 cm
- Width: 10.7 cm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 250/25
- Light color: 2700
- Mains power: 4 V
- Fixture dimmable: No
- Energy class included light source: not applicable
- Maximum wattage replacement bulb: 2.3 W
- IP code: IP44
- Class of protection: Class III

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169265509
- Net weight: 0.38 kg
- Gross weight: 0.49 kg
- Height: 20.5 cm
- Length: 12 cm
- Width: 12.5 cm



Issue date: 2024-12-27  
Version: 0.251

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)