

# PHILIPS

Light Strip Light  
Strip 5m


Light Strips

3000K

White

Dimmable

8720169394742



## Superior light and style

COB light strip offers superior light quality and extremely good uniformity

### High quality light

- EyeComfort – light that's easy on your eyes

### Light effect

- Bright light with uniform distribution

### Durability

- Long lasting quality, even after years

# Highlights

## EyeComfort – light that's easy on your eyes



Poor quality light can cause eye strain. With many of us spending time

indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade.

## Durable and long lasting

Made of robust materials selected for durability and visual appeal. Built for long-lasting performance. Install it and forget it until the end of its long useful life—no hassling with replacements. High-quality materials have UV baking, high temperature, and other endurance tests to ensure durability

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: No
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

## String light/Lightstrip

- Extensibility: No

## Miscellaneous

- Especially designed for: Bedroom, Dining Room, Kitchen, Living Room
- Style: Contemporary
- Type: Light Strips
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 2080 mA

## Product dimensions and weight

- Net weight: 0.056 kg
- Height: 0.17 cm
- Length: 500 cm
- Width: 0.8 cm

## Service

- Warranty: 2 year(s)

#### Technical specifications

- Lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 950
- Light color: 3000
- Mains power: DC 24
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class III

#### Packaging dimensions and weight

- EAN/UPC - product: 8720169394742
- Net weight: 0.58 kg
- Gross weight: 0.61 kg
- Height: 13 cm
- Length: 13 cm
- Width: 1.5 cm



Issue date: 2024-12-13  
Version: 0.92

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)