

Lighting solutions

Wood and concrete pole top brackets

FIG. 1




FIG. 2




FIG. 3




FIG. 4




FIG. 5





FIG. 6



Notes: Mounting hardware not included. Available primer painted - Consult your lighting representative at Cooper Lighting Solutions or visit www.cooperlighting.com

WOOD POLES

Catalog Number	Figure	Arm Length "A" (Feet)	Arm Rise "B" (Feet)	Bracket Net. Weight (Pounds)	Maximum Luminaire Weight (Pounds)	Maximum Luminaire EPA (Square Feet)
WE424	2	4'	2'	10	60	3.0
WE636	2	6'	2'	12	60	3.0
WEH836	2	8'	2'	16	60	3.0
WEHT636	1	6'	2'	25	60	3.0
WEHT836	1	8'	2'	29	60	3.0
WEHT1036	1	10'	2'	33	60	3.0
WEHT1236	1	12'	2'	37	60	3.0
WEHT1536	1	15'	2'	52	60	3.0
WP218	2	2'	1'	7	60	3.0
WP424	2	3' 6"	1' 6"	9	60	2.4
WP624	2	5' 6"	1' 6"	12	60	1.4

CONCRETE ROUND / SQUARE POLES

Catalog Number	Figure	Arm Length "A" (Feet)	Arm Rise "B" (Feet)	Bracket Net. Weight (Pounds)	Maximum Luminaire Weight (Pounds)	Maximum Luminaire EPA (Square Feet)
CE424	2	4'	2'	12	60	3.0
CE636	2	6'	3'	14	60	3.0
CEH836	2	8'	3'	18	60	3.0
CEHT636	3	6'	3'	29	60	3.0
CEHT836	3	8'	3'	33	60	3.0
CEHT1036	3	10'	3'	37	60	3.0
CEHT1236	3	12'	3'	41	60	3.0
CEHT1536	3	15'	3'	56	60	3.0

WOOD AND/OR CONCRETE POLES


Catalog Number	Figure	Arm Length "A" (Feet)	Arm Rise "B" (Feet)	Bracket Net. Weight (Pounds)	Maximum Luminaire Weight (Pounds)	Maximum Luminaire EPA (Square Feet)
WCE424	5	4'	2'	10	75	3.0
WCE636	4	6'	2'	12	75	3.0
WCE836	4	8'	2'	29	75	3.0
WCE1036	4	10'	2'	31	75	3.0
WCE1236	4	12'	2'	37	75	3.0

"W" SERIES GALVANIZED BRACKETS FOR CONCRETE POLES (FIG. 6)

Catalog Number	Pipe Size (Inches)	Arm Length "A" (Feet)	Arm Rise "B" (Inches)	Bracket Net. Weight (Pounds)	Maximum Luminaire Weight (Pounds)	Maximum Luminaire EPA (Square Feet)
W125C040	1-1/4"	4'	25"	16	70	3.1
W200C060	2"	6'	34"	29	90	4.0
W200C080	2"	8'	34"	48	45	2.4

Lighting solutions


Wood and concrete pole top brackets



"P" SERIES STEEL BRACKETS FOR WOOD POLES (Hot dip galvanized)

Catalog Number	Pipe Size (Inches)	Arm Length "A" (Feet)	Arm Rise "B" (Inches)	Bracket Net. Weight (Pounds)	Maximum Luminaire Weight (Pounds)	Maximum Luminaire EPA (Square Feet)
P125S020	1-1/4"	2.0'	13"	7	90	5.0
P125S026	1-1/4"	2.5'	15"	8	80	2.4
P125S040	1-1/4"	4.0'	19"	1	80	2.4
P125S060	1-1/4"	6.0'	24"	15	80	2.4
P125S080	1-1/4"	8.0'	30"	19	35	1.2
P200S020	2"	2.0'	13"	10	90	5.0
P200S026	2"	2.5'	15"	12	80	2.4
P200S040	2"	4.0'	19"	13	80	2.4
P200S060	2"	6.0'	24"	23	80	2.4
P200S080	2"	8.0'	30"	28	70	1.8

NOTES: Mounting hardware not included.



"S" SERIES SINGLE GUY ROD GALVANIZED STEEL BRACKETS FOR WOOD POLES

Catalog Number	Pipe Size (Inches)	Arm Length "A" (Feet)	Arm Rise "B" (Inches)	Bracket Net. Weight (Pounds)	Maximum Luminaire Weight (Pounds)	Maximum Luminaire EPA (Square Feet)
SINGLE GUY WIRE						
S125S060	1-1/4"	6'	24"	20	80	2.4
S125S060	1-1/4"	8'	30"	25	70	1.8
S125S100	1-1/4"	10'	35"	30	50	1.5
SINGLE GUY WIRE						
D200S060	2"	6'	24"	28	80	2.4
D200S080	2"	8'	30"	36	80	2.4
D200S100	2"	10'	35"	43	80	2.4
D200S120	2"	12'	40"	50	80	2.4

NOTES: Mounting hardware not included.