

## DESCRIPTION

Adjustable pinhole with specular clear reflector designed for use with IC or Non-IC AIR-TITE™ 3" Halo small aperture line and low voltage housings. Trim ring is available in multiple finishes to match interior decor. Pinhole trim uses MR16 low voltage or GU10 line voltage lamps ideal for accent and task lighting. Trim offers 15° tilt, and 360° orientation within housing.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

Cast aluminum trim ring available in Matte White finish. Pinhole trim ring incorporates a 1-3/4" aperture with specular reflector to maximize light output. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim).

3002 is designed for use with the following Halo H3 small aperture housings:


- Line Voltage Housing (for 120V GU10 lamps).
 

H36ICAT	50W	IC Air-Tite Housing
H36TAT	50W	Non-IC Air-Tite Housing
H36RTAT	50W	Non-IC Air-Tite Remodel Housing
- Low Voltage Housing (for 12V MR16 lamps).
 

H36LVICAT	50W	IC Air-Tite Housing
H36LVTAT	50W	Non-IC Air-Tite Housing
H36LVRTAT	50W	Non-IC Air-Tite Remodel Housing
H36LVTAT277	50W	Non-IC Air-Tite Housing, 120/277V
H36LVRTAT277	50W	Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps).
 

H38ICAT	50W	IC Air-Tite Housing
---------	-----	---------------------
- Low Voltage Housing (for 12V MR16 lamps).
 

H38LVICAT	37W	IC Air-Tite Housing
-----------	-----	---------------------



Aperture: 1-3/4" [45mm]  
 Ceiling Opening: 3-3/4" [95mm]  
 Outside Diameter: 4-1/4" [108mm]



**3002WHC**  
White with Clear Reflector

## 3002

### 3" Adjustable Pinhole Reflector Trim

3" TRIMS

## ORDERING INFORMATION

### SAMPLE NUMBER: 3002WHC

Order housing and trims separately.

Trim	Finish
3002= 3" Adjustable Pinhole Reflector Trim	WHC=White with Specular Clear Reflector