

# Accessories

## H930 R/PAR Lamp Aiming Accessory



For H7T, H7RT, H7ICT, H7ICAT, H7RICT, H7RICAT housings with 310 and 426 trims. Allows lamp to be aimed up to 30° from vertical and rotated 358°. See housing-trim selection for lamp listings.

## Socket Extender



**H1999**  
**Details** For use with selected trims and housings. Extends lamp 1" (25mm).

## Coil Springs (RS7H)



Set of 4 coil springs for use with coil spring compatible trims



## SD2925 Screwdriver



Screwdriver for tamper resistant screws supplied with H2925 and H2926 brick lights

## Oversized LED Retrofit Housing Adapter



**OH470WH**  
**Size** 6" ID x 9-1/4" OD  
**Details** Oversize housing adapter. For use with open frame retrofit enclosures ML7E26RFK and ML7BXRFK.

## 6" Open Frame LED Retrofit



**ML7BXRFK**  
**Details** 6" Non-IC LED retrofit enclosure with hard-wired BX connection for retrofit of 6" open frame fixtures



**ML7E26RFK**  
**Details** 6" Non-IC LED retrofit enclosure with E26 screw base for 6" open frame fixtures

## Mounting Clips




**TB7**  
**Details** T-Bar attachment clips. Can also be used with HB424 and HB224 hanger bars. Can be used with H7TCP and H750TCP housings hanger bars. Set of four. Order one set per fixture.

## Bar Hangers



Hanger bars are compatible with the brick and step lighting  
**HB224**  
**Details** One piece hanger bar for 24" maximum joist spacing. Set of two.  
**HB424**  
**Details** Two piece hanger bar for 24" max. joist spacing. Set of four pieces. Order one HB424 per fixture.

## GA-ATTRIM-6PK



Accessory / spare trim gasket for use with 6" family trims

## Incandescent Lamps



**Z7** 20W T 6-1/2" IF  
**Z9** 40W R16 FL  
**Z10** 100W BR25  
**Z28** 120V GU10 base, line voltage MR16

## Low Voltage Lamps



**Z21** 12V Q50W MR16 NSP  
**Z26** 12V Q50W MR16 NFL  
**Z31** 12V Q50W MR16 FL  
**Z40** 12V Q75W MR16 NSP  
**Z45** 12V Q75W MR16 FL  
**Z121** 50W MR16/Q/10°/TL\* (GE Turn-and-Lock base)  
**Z131** 50W MR16/Q/20°/TL\* (GE Turn-and-Lock base)  
**Z124** 50W MR16/Q/40°/TL\* (GE Turn-and-Lock base)

\* Replacement service part ONLY