



RCS LED - COMBO

FEATURES


- Sign illuminated by a field-replaceable, high-brightness LED strip
- Extra capacity available for use with remote fixtures
- Capacity to run a maximum of three emergency lights
- Runs with two remote emergency light heads
- Single or double face for maximum flexibility
- Dual voltage input 120/277 VAC, 60Hz
- Heavy-duty, 20-gauge steel housing and face plate
- White powder coat finish

ENERGY DATA

See Specification Sheet for Energy Data

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL924 Listed; NFPA 101 Compliant, NYC Code Compliant



ORDERING INFORMATION

SAMPLE NUMBER: RCS183LED

Family	Faces	Letter Size	Heads	Lamp Type	Remote Capacity ¹	Options and Accessories
RCS=Rival LED Combo	1=Single Face 2=Double Face	8=8"	2=Two Heads 3=Three Heads	LED=LED	1=One Head 2=Two Heads	RFLED401=Single LED Remote Head RFLED402=Double LED Remote Head

NOTES: 1. LED Combo has a 4 LED head maximum capacity.

RCS - STEEL
COMBO

FEATURES


- Heavy-duty, 20-gauge steel housing
- White powder coat finish
- Dual voltage input 120/277 VAC, 60Hz
- Long-life, energy-efficient LEDs (Exit face)
- Three powerful 12-watt incandescent lamps (Emergency Heads)
- Sealed lead calcium batteries (36-watt) with available remote capacity
- Universal, field-selectable chevrons

ENERGY DATA

See Specification Sheet for Energy Data

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL924 Listed; Damp Location, NYC Code Compliant



ORDERING INFORMATION

SAMPLE NUMBER: RCS8R3

Family	Letter Size	Letter Color	Number of Heads
RCS=Rival Steel Combo	8=8"	R=Red	3=Three Heads