

DESCRIPTION

Adjustable pinhole with baffle designed for use with IC or Non-IC AIR-TITE™ 3" Halo small aperture line and low voltage housings. Trim ring is available in multiple finishes to match interior decor. Trim uses low voltage MR16 or GU10 line voltage lamps ideal for accent and task lighting. Pinhole trim offers 15° tilt, and 360° orientation within housing.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Cast aluminum trim ring available in Matte White, Black, Satin Nickel, or Tuscan Bronze finishes. Pinhole trim ring incorporates a 1-3/4" aperture with matte black baffle to control glare. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim).

3001 is designed for use with the following Halo H3 housings:


- Line Voltage Housing (for 120V GU10 lamps).

H36ICAT	50W	IC Air-Tite Housing
H36TAT	50W	Non-IC Air-Tite Housing
H36RTAT	50W	Non-IC Air-Tite Remodel Housing
- Low Voltage Housing (for 12V MR16 lamps).

H36LVICAT	50W	IC Air-Tite Housing
H36LVTAT	50W	Non-IC Air-Tite Housing
H36LVRTAT	50W	Non-IC Air-Tite Remodel Housing
H36LVTAT277	50W	Non-IC Air-Tite Housing, 120/277V
H36LVRTAT277	50W	Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps).

H38ICAT	50W	IC Air-Tite Housing
---------	-----	---------------------
- Low Voltage Housing (for 12V MR16 lamps).

H38LVICAT	37W	IC Air-Tite Housing
-----------	-----	---------------------



Aperture: 1-3/4" [45mm]
 Ceiling Opening: 3-3/4" [95mm]
 Outside Diameter: 4-1/4" [108mm]

ORDERING INFORMATION

SAMPLE NUMBER: 3001WHBB

Order housing and trims separately.

Trim	Finish
3001= 3" Adjustable Baffle Trim	BKBB =Black with Black Baffle SNBB =Satin Nickel with Black Baffle TBZBB =Tuscan Bronze with Black Baffle WHBB =White with Black Baffle WHWB =White with White Baffle




3001WHWB
White with White Baffle



3001WHBB
White with Black Baffle



3001BKBB
Black with Black Baffle



3001SNBB
Satin Nickel with Black Baffle



3001TBZBB
Tuscan Bronze with Black Baffle

3001

3" Adjustable Pinhole Baffle Trim

3" TRIMS