

DESCRIPTION


Low Voltage Adjustable Spot trim (transformer included) with 30° tilt in the 6" trim family for use in recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

1412 is listed for use with the following 6" aperture housings.

- Incandescent Housings
 - H7T - Non-IC Housing - 50W 12V MR16
 - H7TCP - Non-IC Chicago Plenum Housing - 50W 12V MR16
 - H7RT - Non-IC Remodel Housing - 50W 12V MR16



1412W
White Trim with White Baffle and Lampholder



1412P
White Trim with Black Baffle and Lampholder

ORDERING INFORMATION

SAMPLE NUMBER: 1412W

Trim	Finish	Accessory
1412= 6" Low Voltage Adjustable Spot, 30° Tilt	W =White Trim with White Baffle and Lampholder P =White Trim with Black Baffle and Lampholder	Designer Trim Rings TRM6C =Chrome TRM6MB =Black Metal TRM6P =White Metal TRM6SN =Satin Nickel TRM6TBZ =Tuscan Bronze TRM7MB =Black Plastic

1412
Low Voltage Adjustable Spot 30° Tilt Light

6" TRIMS