

DESCRIPTION

Adjustable flush gimbal trim is designed for use with IC or Non-IC AIR-TITE™ 3" Halo small aperture line and low voltage housings. This die-cast trim is available in multiple finishes to match interior decor. Adjustable gimbal trim uses MR16 low voltage or GU10 line voltage lamps ideal for accent and task lighting. Trim offers 35° tilt, and -15° reverse tilt and 360° orientation within housing.

Catalog #		Type
Project		
Comments		Date
Prepared by		


SPECIFICATION FEATURES

Adjustable gimbal is available in Matte White, Black, Satin Nickel, or Tuscan Bronze finishes with Black Baffle. White gimbal also available with White Baffle. Three pressure springs ensure positive retention in housing.


Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim.)

3009 is designed for use with the following Halo H3 small aperture housings:

- Line Voltage Housing (for 120V GU10 lamps).
 - H36ICAT 50W IC Air-Tite Housing
 - H36TAT 50W Non-IC Air-Tite Housing
 - H36RTAT 50W Non-IC Air-Tite Remodel Housing
- Low Voltage Housing (for 12V MR16 lamps).
 - H36LVICAT 50W IC Air-Tite Housing
 - H36LVTAT 50W Non-IC Air-Tite Housing
 - H36LVRTAT 50W Non-IC Air-Tite Remodel Housing
 - H36LVTAT277 50W Non-IC Air-Tite Housing, 120/277V
 - H36LVRTAT277 50W Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps).
 - H38ICAT 50W IC Air-Tite Housing
- Low Voltage Housing (for 12V MR16 lamps).
 - H38LVICAT 50W IC Air-Tite Housing




Baffle Aperture: 1-3/4" [45mm]
 Baffle Diameter: 2" [51mm]
 Gimbal Diameter: 2-3/4" [70mm]
 Ceiling Opening: 3-3/4" [95mm]
 Outside Diameter: 4-1/4" [108mm]



3009WHWB
White with White Baffle



3009WHBB
White with Black Baffle



3009BKBB
Black with Black Baffle



3009SNBB
Satin Nickel with Black Baffle



3009TBZBB
Tuscan Bronze with Black Baffle

ORDERING INFORMATION

SAMPLE NUMBER: 3009WHBB
 Order housing and trims separately.

Trim	Finish
3009 = 3" Adjustable Gimbal Trim	BKBB =Black with Black Baffle SNBB =Satin Nickel with Black Baffle TBZBB =Tuscan Bronze with Black Baffle WHBB =White with Black Baffle WHWB =White with White Baffle

3009

3" Adjustable Gimbal

3" TRIMS