



FluxPanel Selectable LED (SBP)

1x4, wattage and CCT selectable backlit panel, 80 CRI, 30-35-40 watts and 3500K-4000K-5000K CCT

1x4, wattage and CCT selectable backlit panel, 80 CRI, 30-35-40 watts and 3500K-4000K-5000K CCT - 110 lm/W

The Selectable backlit panel is a highly versatile luminaire designed to provide three lumen and three CCT packages per size. Available for use in recessed, suspended, and surface mount applications, the SBP is a versatile luminaire that is ideal for general lighting applications such as open office, schools, healthcare, and retail.

Product data

General information		Enclosure	
Lamp Source Code	LED	Metal and Plastic	
Colour Temperature	3500 4000 5000 K	Approval and application	
CRI	80	Energy Certifications	DLC Standard
Photometric Distribution Type	Diffuse	Initial performance (IEC compliant)	
Mounting	T-Bar / T-Grid Surface	Luminaire Lumens	3000 3500 4000 lm
Number Of Pieces	1	Efficacy	110 lm/W
Operating and electrical		Product data	
Voltages	120-277 V	Full product code	911401837681
Luminaire Input Watts	29 33 36 W	Order product name	1SBP3040L8CS-4-UNV-DIM
Mechanical and housing		EAN/UPC - Product	190096130993
Fixture Size	1 ft x 4 ft	Order code	1SBP3040L8CS-4-UNV-DIM

FluxPanel Selectable LED (SBP)

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	911401837681
Catalog Number	1SBP3040L8CS-4-UNV-DIM

Catalog Number Description	1x4, wattage and CCT selectable backlit panel, 80 CRI, 30-35-40 watts and 3500K-4000K-5000K CCT
-----------------------------------	--

