



# Essential SmartBright G4 LED Floodlight BVP150

## BVP150 LED45/CW PSU 50W SWB MDU G2 GM

Essential SmartBright G4 LED Floodlight BVP150, 4750 lm, 50 W, 865 cool daylight, Safety class I

The Essential SmartBright G4 LED floodlight comes in a compact and sturdy design. Lightweight, with a robust die-cast aluminum housing and corrosion-proof coating, it's suitable for general outdoor applications. Plus, with a higher efficacy than the previous generation, it also saves more energy.

### Product data

General Information		Operating and Electrical	
Driver included	Yes	Input Voltage	220-240 V
Lighting Technology	LED	Line Frequency	50 or 60 Hz
CE mark	-	Inrush current	1.08 A
<b>Light Technical</b>		Power Consumption	50 W
Luminous Flux	4,750 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	6500 K	Connection	Flying leads/wires
Luminous Efficacy (rated) (Nom)	95 lm/W	Cable	Cable 0.6 m without plug
Color rendering index (CRI)	>80	<b>Temperature</b>	
Light source color	865 cool daylight	Ambient temperature range	-25 to +40 °C
Optical cover type	Glass	<b>Controls and Dimming</b>	
		Dimmable	No

# Essential SmartBright G4 LED Floodlight BVP150

Control interface	-
-------------------	---

## Mechanical and Housing

Housing Material	Aluminum die-cast
Optical cover material	Tempered glass
Housing Color	Black
Overall length	223 mm
Overall width	210 mm
Overall height	57 mm
Effective projected area	0.018 m <sup>2</sup>
Dimensions (Height x Width x Depth)	57 x 210 x 223 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class I


## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.313, 0.337) SDCM <6
Power consumption tolerance	+/-10%

## Product Data

Order product name	BVP150 LED45/CW PSU 50W SWB MDU G2 GM
Full product name	BVP150 LED45/CW PSU 50W SWB MDU G2 GM
Full product code	871951454389899
Order code	911401873283
Material Nr. (12NC)	911401873283
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514543898
Numerator - Packs per outer box	24
EAN/UPC - Case	8719514543980

## Dimensional drawing



BVP150 MDU			
	50W	50W	50W
A	141	188	220
B	130	185	205
C	54	56	57
D	75	100	125
E	5	6	6.5
F	5.5	6.5	9

