



Garage and Canopy Round DualSelect

GC Round DS 28-40-60W/30-40-50K/120-347

GC Round DS 28-40-60W/30-40-50K/120-347 - 130 lm/W

Garage and Canopy Round Dual Select LED luminaire is exactly what you need when searching for durable, cost-effective lighting for parking garages, covered walkways and outdoor canopies. Compact and efficient, it has durable, weather tight construction and a rugged, UV-stabilized, frosted lens.

Product data

General information	
Lamp Source Code	LED
Colour Temperature	3000 4000 5000 K
CRI	70
Photometric Distribution Type	Type V
Mounting	Recessed Surface
Awards	DLC QPL
Number Of Pieces	1

Operating and electrical	
Voltages	120/347 V
Luminaire Input Watts	28 40 60 W

Mechanical and housing	
Enclosure	Die cast Aluminum alloy

Initial performance (IEC compliant)	
Luminaire Lumens	3870-4730 5130-6270 7470-9130 lm

Efficacy	130 lm/W
----------	----------

Application conditions	
Ambient temperature range	-40 °C to 40 °C
Max Ambient Temp	40 °C
Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C

Product data	
Order product name	GCR60-SCT-G1-SM-5-10-BZ
EAN/UPC - Product	190096181957
Order code	GCR60-SCT-G1-SM-5-10-BZ
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	5
Material Nr. (12NC)	912401591779
Net Weight (Piece)	3.020 kg
Catalog Number	GCR60-SCT-G1-SM-5-10-BZ
Catalog Number Description	GC Round DS 28-40-60W/30-40-50K/120-347

Garage and Canopy Round DualSelect

Quick Ship

2 days, Stock Ready North America

