



T8 High CRI Lamps

F32T8/TL935/ALTO 30PK

Philips T8 High CRI lamps featuring ALTO II technology are ideal when better color rendering properties are preferred.

Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Finish	Coated glass
Features	ALTO® (ALTO)	Bulb Shape	T-8 (T8)
Light Technical		Approval and Application	
Color Code	935 [CCT of 3500K]	Mercury (Hg) Content (Nom)	1.7 mg
Beam Angle (Nom)	0 degree(s)		
Luminous Flux	2,625 lm	Product Data	
Correlated Color Temperature (Nom)	3500 K	Order product name	F32T8/TL935/ALTO 30PK
Color rendering index (CRI)	>90	Full product name	F32T8/TL935/ALTO 30PK
Operating and Electrical		Order code	927871204901
Power Consumption	32 W	Material Nr. (12NC)	927871204901
Lamp Current (Nom)	265 mA	Numerator - Quantity Per Pack	1
Wattage Equivalent	32 W	EAN/UPC - Product/Case	046677479602
Voltage (Nom)	137 V	Numerator - Packs per outer box	30
Voltage (Nom)	137 V	EAN/UPC - Case	50046677479607

T8 High CRI Lamps

Dimensional drawing

Product	C (max)	D (max)
F32T8/TL935/ALTO 30PK	1,213.6 mm	27.9 mm

