



# Switch Start Metal Halide Standard

## MH175/C/U 12PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

### Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data

General Information		Warm-up time to 60% light	
Cap-Base	E39 [Single Contact Mogul Screw]		<120 s
Light Technical		Controls and Dimming	
Luminous Flux	8,645 lm	Dimmable	No
Chromaticity Coordinate X (Nom)	0.385	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	0.39	Bulb Finish	Coated glass
Correlated Color Temperature (Nom)	3900 K	Bulb Material	Hard Glass
Luminous Efficacy (Rated) (Min)	64 lm/W	Bulb Shape	BD17
Luminous Efficacy (rated) (Nom)	76 lm/W	Approval and Application	
Color rendering index (CRI)	>60	Mercury (Hg) Content (Max)	30 mg
Operating and Electrical		Product Data	
Power Consumption	175 W	Order product name	MH175/C/U 12PK
Wattage Equivalent	175 W		

## Switch Start Metal Halide Standard

Full product name	MH175/C/U 12PK
Order code	928601150403
Material Nr. (12NC)	928601150403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677287283

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677287288

### Dimensional drawing

Product	D (max)	C (max)
MH175/C/U 12PK	90 mm	206 mm

