



CorePro GLASS LED candles and lusters

CorePro LEDLusterND2-25W P45 E14 827 CLG

Featuring a classic heritage design, these filament LED candle combines the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. The LED candle bulb, a very easy choice for people who are looking for a retrofit LED replacement, the LED candle provides 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light for stairway lighting. The LED candle bulb offers a lifetime of 15,000 hours to reduce maintenance costs.

Product data

General Information		Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
Cap-Base	E14	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Nominal lifetime	15,000 hour(s)	Stroboscopic effect visibility measure (SVM)	0.4
Switching Cycle	20,000	Photobiological safety according to EN 62471	RG1
Lighting Technology	LED	Operating and Electrical	
Flux measurement reference	Sphere	Line Frequency	50 to 60 Hz
CE mark	Yes	Input Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power Consumption	2 W
Light Technical		Lamp Current (Nom)	20 mA
Color Code	827 [CCT of 2700K]	Wattage Equivalent	25 W
Luminous Flux	250 lm	Starting Time (Nom)	0.5 s
Color Designation	Warm White (WW)	Warm-up time to 60% light	0.5 s
Correlated Color Temperature (Nom)	2700 K	Power Factor (Fraction)	0.4
Luminous Efficacy (rated) (Nom)	125.00 lm/W	Voltage (Nom)	220-240 V
Color Consistency	<6		
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

CorePro GLASS LED candles and lusters

Temperature

T-Case Maximum (Nom)	36 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	P45

Approval and Application

Energy Efficiency Class	E
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	387363
EyeComfort	Yes

Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----


Product Data

Order product name	CorePro LEDLusterND2-25W P45 E14 827 CLG
Full product name	CorePro LEDLusterND2-25W P45 E14 827 CLG
Full product code	871951434774800
Order code	929001238692
Material Nr. (12NC)	929001238692
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514347748
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514347755


Dimensional drawing

Product	D	C
CorePro LEDLusterND2-25W P45 E14 827 CLG	45 mm	80 mm

Photometric data



Spectral Power Distribution Colour - CorePro LEDLusterND2-25W P45 E14 827 CLG



Light Distribution Diagram - CorePro LEDLusterND2-25W P45 E14 827 CLG


CorePro GLASS LED candles and lusters

Photometric data



General uniform lighting - CorePro LEDLusterND2-25W P45 E14 827 CLG

Lifetime



Life Expectancy Diagram - CorePro LEDLusterND2-25W P45 E14 827 CLG

Lumen Maintenance Diagram - CorePro LEDLusterND2-25W P45 E14 827 CLG

