



Candle LED



LED 15W T25 E14 WW FR ND RF 1SRT6 UK

Philips Candle Dimmable LED Lamps offer decorative energy-saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long-life alternative to standard incandescent sources.

Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime	15,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Colour Code	827 [CCT of 2700K]
Beam angle (nom.)	240 degree(s)
Luminous Flux	150 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	88.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RG0


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	1.7 W
Lamp current (nom.)	20 mA
Wattage equivalent	15 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	T25 [T 25 mm]
Approval and Application	
Energy Efficiency Class	F

Candle LED

Energy consumption kWh/1,000 hours	2 kWh
EPREL registration number	391879
EyeComfort	Yes
Product Data	
Order product name	LED 15W T25 E14 WW FR ND RF 1SRT6 UK
Full product name	LED 15W T25 E14 WW FR ND RF 1SRT6 UK



Full EOC	871869977193502
Order code	77193502
Material no. (12 NC)	929001325796
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699771935
Numerator – packs per outer box	6
EAN/UPC – Case	8719514405820

Dimensional drawing



Product	D	C
LED 15W T25 E14 WW FR ND RF 1SRT6 UK	25 mm	59 mm

Photometric data




Light Distribution Diagram - LED 15W T25 E14 WW FR ND RF 1SRT6 UK

General uniform lighting - LED 15W T25 E14 WW FR ND RF 1SRT6 UK


Candle LED

Photometric data




Spectral Power Distribution Colour - LED 15W T25 E14 WW FR ND RF 1SRT6 UK

Lifetime



Life Expectancy Diagram - LED 15W T25 E14 WW FR ND RF 1SRT6 UK



Lumen Maintenance Diagram - LED 15W T25 E14 WW FR ND RF 1SRT6 UK

