# **PHILIPS** Lighting



# **CorePro LEDspot MV**



# CorePro LEDspot 4-50W GU10 830 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

#### **Product data**

General Information	
Cap-Base	GU10
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	345 lm
Luminous Intensity (Nom)	700 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	345 lm


Flickering value (PstLM) - Flickering value as	1
per EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	23 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.84
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers

## CorePro LEDspot MV

Mechanical and Housing	
Bulb Shape	PAR16
Approval and Application	
Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	391911
EyeComfort	Yes
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	CorePro LEDspot 4-50W GU10 830
	36D DIM


Full product name	CorePro LEDspot 4-50W GU10 830	
	36D DIM	
Full product code	871951435883600	
Order code	929002068302	
Material Nr. (12NC)	929002068302	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8719514358836	
Numerator - Packs per outer box	10	
EAN/UPC - Case	8719514358843	

#### Dimensional drawing




Product	D	с
CorePro LEDspot 4-50W GU10 830 36D DIM	50 mm	54 mm

#### Photometric data




Spectral Power Distribution Colour - CorePro LEDspot 4-50W GU10 830 36D DIM



Light Distribution Diagram - CorePro LEDspot 4-50W GU10 830 36D DIM


### **CorePro LEDspot MV**

#### Photometric data



Accent Lighting Spots - CorePro LEDspot 4-50W GU10 830 36D DIM

#### Lifetime



Life Expectancy Diagram - CorePro LEDspot 4-50W GU10 830 36D DIM

Lumen Maintenance Diagram - CorePro LEDspot 4-50W GU10 830 36D DIM



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, March 15 - data subject to change