



Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

5A19/LED/927/FR/P/ND 4/1FB

Most affordable A19 lamp ideal for residential, back of house closets.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	450 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5 W
Lamp Current (Nom)	77 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No

Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location

Approval and Application

Energy Certifications	No
T20 compliant	No


Application Conditions

can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data



Order product name	5A19/LED/927/FR/P/ND 4/1FB
Full product name	5A19/LED/927/FR/P/ND 4/1FB
Order code	929003004504
Material Nr. (12NC)	929003004504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565084
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565089

Dimensional drawing



Product	D	C
5A19/LED/927/FR/P/ND 4/1FB	60 mm	104 mm

Photometric data




Spectral Power Distribution Colour - 5A19/LED/927/FR/P/ND 4/1FB

Light Distribution Diagram - 5A19/LED/927/FR/P/ND 4/1FB

Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps


Photometric data




Contract Parameters 41 Philips Lighting B.V. Page 10

General uniform lighting - 5A19/LED/927/FR/P/ND 4/1FB

Lifetime



Lumen Maintenance Diagram - 5A19/LED/927/FR/P/ND 4/1FB



Life Expectancy Diagram - 5A19/LED/927/FR/P/ND 4/1FB

