





CorePro LEDtube 1500mm 20W 840 T8

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pack back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes


Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	2,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Datasheet, 2024, March 11 data subject to change

Flickering value (PstLM) - Flickering value as per	1
EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.9
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	20 W
Lamp Current (Nom)	105 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	58 W
Inrush current at mains	8.7
Max. lamp no. on MCB B type 10A - Mains	34
Max. lamp no. on MCB B type 10A – EM ballast	54
without Comp. Cap.	
Max. lamp no. on MCB B type 10A – EM ballast	10
with Comp. Cap.	
Max. lamp no. on MCB B type 16A - Mains	55
Max. lamp no. on MCB B type 16A – EM ballast	87
without Comp. Cap.	
Max. lamp no. on MCB B type 16A – EM ballast	17
with Comp. Cap.	
Ballast Compatibility	EM/Mains
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 ℃


Controls and Dimming				
Dimmable	No			
Mechanical and Housing				
Bulb Finish	Frosted			
Bulb Material	Glass			
Product Length	1,500 mm			
Bulb Shape	Т8			
Approval and Application				
Energy Efficiency Class	E			
Energy Saving Product	Yes			
Approval Marks	RoHS compliance CE marking			
	KEMA Keur certificate			
Energy Consumption kWh/1000 h	20 kWh			
EPREL Registration Number	1384717			
Product Data				
Order product name	CorePro LEDtube 1500mm 20W			
	840 T8			
Full product name	CorePro LEDtube 1500mm 20W			
	840 T8			
Full product code	871951432539500			
Order code	929003022502			
Material Nr. (12NC)	929003022502			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	8719514325395			
Numerator - Packs per outer box	10			
EAN/UPC - Case	8719514325401			

Dimensional drawing




Product	D1	D2	A1	A2	А3
CorePro LEDtube 1500mm 20W	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
840 T8					

Photometric data




Calculus Photometrics 4.5 Philips Lighting Scv. Rago:

General uniform lighting - CorePro LEDtube 1500mm 20W 840 T8




Light Distribution Diagram - CorePro LEDtube 1500mm 20W 840 T8




Spectral Power Distribution Colour - CorePro LEDtube 1500mm 20W 840 T8

Lifetime





Life Expectancy Diagram - CorePro LEDtube 1500mm 20W 840 T8



Life Expectancy Diagram - CorePro LEDtube 1500mm 20W 840 T8

Lifetime





Life Expectancy Diagram - CorePro LEDtube 1500mm 20W 840 T8

Lumen Maintenance Diagram - CorePro LEDtube 1500mm 20W 840 T8

