

MASTER LEDtube T8 Ultra Efficient



MAS LEDtube 1200mm UE 13.5W 840 T8

With energy prices rising and the EU's Green Deal2 continuing to fund energy efficient building renovations, many are looking into make their company's lighting more sustainable. The new Philips MASTER LEDtube Ultra Efficient T8 is a true breakthrough on the way to more sustainable lighting. It replaces your current fluorescent tube or LED tube directly and offers immediately great energy cost reduction as well as a much longer lifetime!

Product data

| General Information | | | | |
|---------------------------------------|--------------------|--|--|--|
| Cap-Base | G13 ROT | | | |
| Nominal lifetime | 75,000 hour(s) | | | |
| Switching Cycle | 200,000 | | | |
| Lighting Technology | LED | | | |
| Flux measurement reference | Sphere | | | |
| CE mark | Yes | | | |
| EU RoHS compliant | Yes | | | |
| | | | | |
| Light Technical | | | | |
| Color Code | 840 [CCT of 4000K] | | | |
| Beam Angle (Nom) | 160 degree(s) | | | |
| Luminous Flux | 2,500 lm | | | |
| Color Designation | Cool White (CW) | | | |
| Correlated Color Temperature (Nom) | 4000 K | | | |
| Luminous Efficacy (rated) (Nom) | 185 lm/W | | | |
| Color Consistency | <6 | | | |
| Color rendering index (CRI) | 80 | | | |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | | | |
| | | | | |

| Flickering value (PstLM) - Flickering value as per | 0.5 |
|--|-------------|
| EN 61000-3-3 | |
| Stroboscopic effect visibility measure (SVM) | 0.2 |
| Photobiological safety according to EN 62471 | RG0 |
| | |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 13.5 W |
| Lamp Current (Max) | 69 mA |
| Lamp Current (Min) | 56 mA |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.9 |
| Voltage (Nom) | 220-240 V |
| LED alternative to fluorescent lamp power | 36 W |
| Inrush current at mains | 3.87 |
| Max. lamp no. on MCB B type 10A - Mains | 110 |


Datasheet, 2024, March 15 data subject to change

MASTER LEDtube T8 Ultra Efficient

| Max. lamp no. on MCB B type 10A – EM ballast | 110 |
|--|-----------------|
| without Comp. Cap. | |
| Max. lamp no. on MCB B type 10A – EM ballast | 15 |
| with Comp. Cap. | |
| Max. lamp no. on MCB B type 16A - Mains | 175 |
| Max. lamp no. on MCB B type 16A – EM ballast | 175 |
| without Comp. Cap. | |
| Max. lamp no. on MCB B type 16A – EM ballast | 25 |
| with Comp. Cap. | |
| Ballast Compatibility | EM/Mains |
| | |
| Temperature | |
| Ambient temperature range | -20 °C to 45 °C |
| T-Case Maximum (Nom) | 55 °C |
| | |
| Controls and Dimming | |
| Dimmable | No |
| | |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Material | Plastic |
| Product Length | 1,200 mm |
| Bulb Shape | Т8 |
| | |

| Approval and Application | | |
|---------------------------------|--------------------------------|--|
| Energy Efficiency Class | В | |
| Energy Saving Product | Yes | |
| Approval Marks | RoHS compliance TUV CE marking | |
| | KEMA Keur certificate | |
| Energy Consumption kWh/1000 h | 14 kWh | |
| EPREL Registration Number | 1205540 | |
| | | |
| Product Data | | |
| Order product name | MAS LEDtube 1200mm UE 13.5W | |
| | 840 T8 | |
| Full product name | MAS LEDtube 1200mm UE 13.5W | |
| | 840 T8 | |
| Full product code | 871951433972900 | |
| Order code | 929003067002 | |
| Material Nr. (12NC) | 929003067002 | |
| Numerator - Quantity Per Pack | 1 | |
| EAN/UPC - Product/Case | 8719514339729 | |
| Numerator - Packs per outer box | 10 | |
| EAN/UPC - Case | 8719514339736 | |
| | | |


Dimensional drawing




| Product | D1 | D2 | A1 | A2 | A3 |
|-----------------------------|---------|-------|------------|------------|------------|
| MAS LEDtube 1200mm UE 13.5W | 25.8 mm | 28 mm | 1,198.2 mm | 1,205.3 mm | 1,212.4 mm |
| 840 T8 | | | | | |

MASTER LEDtube T8 Ultra Efficient


Photometric data



General uniform lighting - MAS LEDtube 1200mm UE 13.5W 840 T8




Spectral Power Distribution Colour - MAS LEDtube 1200mm UE 13.5W 840 T8




Light Distribution Diagram - MAS LEDtube 1200mm UE 13.5W 840 T8

Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1200mm UE 13.5W 840 T8


Life Expectancy Diagram - MAS LEDtube 1200mm UE 13.5W 840 T8




Datasheet, 2024, March 15

MASTER LEDtube T8 Ultra Efficient


Lifetime





Life Expectancy Diagram - MAS LEDtube 1200mm UE 13.5W 840 T8

Lumen Maintenance Diagram - MAS LEDtube 1200mm UE 13.5W 840 T8



Life Expectancy Diagram - MAS LEDtube 1200mm UE 13.5W 840 T8



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.