



MASTER Value Glass LED bulbs

MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G

Featuring a classic heritage design, these filament LED bulbs combine the familiar shapes of incandescent bulbs with the benefits of long-lasting LED technology. These MASTER Value Glass LED bulbs offer more energy savings than normal glass LED bulbs. At the same time, they also provide customers with good light experience, enhanced by excellent dimming performance (dimmable glass LED bulbs). MASTER Value Glass LED Bulbs deliver significant energy savings, using 30% less energy compared to normal LED bulbs and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmable LED bulbs also reduce maintenance costs.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	E27		90
Nominal lifetime	15,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	70 %
Switching Cycle	20,000	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Lighting Technology	LED	Stroboscopic effect visibility measure (SVM)	0.4
Flux measurement reference	Sphere	Photobiological safety according to EN 62471	RG0
CE mark	Yes	Operating and Electrical	
EU RoHS compliant	Yes	Line Frequency	50 to 60 Hz
Light Technical		Input Frequency	50 to 60 Hz
Color Code	927 [CCT of 2700K]	Power Consumption	3.4 W
Luminous Flux	470 lm	Lamp Current (Nom)	20 mA
Color Designation	Warm White (WW)	Wattage Equivalent	40 W
Correlated Color Temperature (Nom)	2700 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	138.00 lm/W	Warm-up time to 60% light	0.5 s
Color Consistency	<6	Power Factor (Fraction)	0.7

MASTER Value Glass LED bulbs

Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	574383
EyeComfort	Yes


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data



Order product name	MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G
Full product name	MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G
Full product code	871951435481400
Order code	929003070502
Material Nr. (12NC)	929003070502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514354814
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514354821

Dimensional drawing



Product	D	C
MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G	60 mm	104 mm

Photometric data




Light Distribution Diagram - MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G

General uniform lighting - MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G

MASTER Value Glass LED bulbs

Photometric data




Spectral Power Distribution Colour - MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G

Lifetime



Life Expectancy Diagram - MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G



Lumen Maintenance Diagram - MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G

