



# MASTER UltraEfficient LED bulb

## MAS LEDBulbND7.3-100WE27830 A70 FRG UE

This is the most efficient LED bulb from Philips brand. 210lm/W helps to concrete the company statement of sustainability. 50000 hour lifetime helps to extend the replacement cycle to reduce the waste. This is not only the high SPEC product, but also keep the light quality of Philips brand

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,535 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	210 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Flickering value (PstLM) - Flickering value 1 as per EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG1


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7.3 W
Lamp Current (Nom)	70 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V

# MASTER UltraEfficient LED bulb

Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A70
Approval and Application	
Energy Efficiency Class	A
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	1370038
EyeComfort	Yes
Application Conditions	
can it be used in closed luminaires	No



Product Data	
Order product name	MAS LEDBulbND7.3-100WE27830 A70 FRG UE
Full product name	MAS LEDBulbND7.3-100WE27830 A70 FRG UE
Full product code	871951443583400
Order code	929003480202
Material Nr. (12NC)	929003480202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514435834
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514435841

## Dimensional drawing



Product	D	C
MAS LEDBulbND7.3-100WE27830 A70 FRG UE	70 mm	127 mm

## Photometric data




Spectral Power Distribution Colour - MAS LEDBulbND7.3-100WE27830 A70 FRG UE

General uniform lighting - MAS LEDBulbND7.3-100WE27830 A70 FRG UE

# MASTER UltraEfficient LED bulb

## Photometric data



Light Distribution Diagram - MAS LEDBulbND7.3-100WE27830 A70 FRG UE

## Lifetime



Life Expectancy Diagram - MAS LEDBulbND7.3-100WE27830 A70 FRG UE

Lumen Maintenance Diagram - MAS LEDBulbND7.3-100WE27830 A70 FRG UE

