



MASTER UltraEfficient LED bulb

MAS LEDBulbND7.3-100WE27840 A70 FRG UE

This is the most efficient LED bulb from Philips brand. 210lm/W helps to concrete the company statement of sustainability. 50000 hour lifetime helps to extend the replacement cycle to reduce the waste. This is not only the high SPEC product, but also keep the light quality of Philips brand

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E27 |
| Nominal lifetime | 50,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| Flux measurement reference | Sphere |
| CE mark | Yes |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 1,535 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 210 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| | |
|---|-----|
| Flickering value (PstLM) - Flickering value 1 as per EN 61000-3-3 | |
| Stroboscopic effect visibility measure (SVM) | 0.4 |
| Photobiological safety according to EN 62471 | RG1 |


| Operating and Electrical | |
|---------------------------|-------------|
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 7.3 W |
| Lamp Current (Nom) | 70 mA |
| Wattage Equivalent | 100 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.4 |
| Voltage (Nom) | 220-240 V |

MASTER UltraEfficient LED bulb

| Temperature | |
|-------------------------------------|---------|
| T-Case Maximum (Nom) | 70 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Shape | A70 |
| Approval and Application | |
| Energy Efficiency Class | A |
| Energy Consumption kWh/1000 h | 8 kWh |
| EPREL Registration Number | 1370037 |
| EyeComfort | Yes |
| Application Conditions | |
| can it be used in closed luminaires | No |


| Product Data | |
|---------------------------------|--|
| Order product name | MAS LEDBulbND7.3-100WE27840 A70 FRG UE |
| Full product name | MAS LEDBulbND7.3-100WE27840 A70 FRG UE |
| Full product code | 871951443585800 |
| Order code | 929003480302 |
| Material Nr. (12NC) | 929003480302 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8719514435858 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8719514435865 |

Dimensional drawing




| Product | D | C |
|--|-------|--------|
| MAS LEDBulbND7.3-100WE27840 A70 FRG UE | 70 mm | 127 mm |

Photometric data




General uniform lighting - MAS LEDBulbND7.3-100WE27840 A70 FRG UE



Spectral Power Distribution Colour - MAS LEDBulbND7.3-100WE27840 A70 FRG UE

MASTER UltraEfficient LED bulb

Photometric data



Light Distribution Diagram - MAS LEDBulbND7.3-100WE27840 A70 FRG UE

Lifetime



Life Expectancy Diagram - MAS LEDBulbND7.3-100WE27840 A70 FRG UE



Lumen Maintenance Diagram - MAS LEDBulbND7.3-100WE27840 A70 FRG UE

