



LED Glass HID lamps

19GC/LED/840/ND E26 BB 6/1

Philips Glass HID lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. Thanks to our High-Power LED filament technology, this new generation of indoor/outdoor glass lamps brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant savings with a low initial investment. They are designed to have the same aesthetics, lamp size and light distribution as the HID lamps they are replacing, so the upgrade to LED is easier than ever!

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	15,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	3,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	157.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	19 W
Lamp Current (Nom)	176 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	131 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass

LED Glass HID lamps

Bulb Shape	ED75
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	19GC/LED/840/ND E26 BB 6/1
Full product name	19GC/LED/840/ND E26 BB 6/1



Order code	578856
Material Nr. (12NC)	929003507804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677578855
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677578850

Dimensional drawing




Product	D	C
19GC/LED/840/ND E26 BB 6/1	3 inch	7-1/4 inch

Photometric data



Spectral Power Distribution Colour - 19GC/LED/840/ND E26 BB 6/1


Light Distribution Diagram - 19GC/LED/840/ND E26 BB 6/1



General uniform lighting - 19GC/LED/840/ND E26 BB 6/1

LED Glass HID lamps

Lifetime



Life Expectancy Diagram - 19GC/LED/840/ND E26 BB 6/1

Lumen Maintenance Diagram - 19GC/LED/840/ND E26 BB 6/1

