



Day-Brite / CFI 3D Printed High Bay, PM Series offers a big output with a tiny input. Select from our 20,000 or 25,000 lumen Philips LED HID replacement lamps or choose your own lumen levels from a variety of options. Light-weight yet durable polycarbonate construction reduces weight that helps ease handling during installation. Unleash your inner creator and select from a variety of color options to help tailor your design.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Qty: _____
 Notes: _____

Fixture

example: 3DP HB L CL TC WHST 200L or 250L NB 840K

Series	Colors	Shade Textures	Top Color	Lumens	Beams	CRI/CCT
3DP HB L						
3DP HB L PM Large Series	CL Clear DIFF Diffuse GYSM Smokey Grey	TC Tufted Coarse CUST Custom Logo (Layered Fine) minimum order size required	BKST Satin Black GYST Satin Grey WHST Satin White	200L 20,000lm 250L 25,000lm	NB Narrow (60°) VWB Very Wide (120°)	840K 80CRI / 4000K 850K 80CRI / 5000K

Note: Different colors, textures and custom logo options are available upon request.

Features

- 1. Customizable:** choose from a wide variety of colors, textures, and styles to help personalize customer options.
- 2. Sustainable:** 3D Printed products produce less carbon emissions when compared to traditional, conventional luminaires.
- 3. Local production:** Printed & assembled in Littlestown, PA.
- 4. Quick delivery:** Created on demand and shipped in weeks.
- 5. Product Weight:** 5 lbs without lamp / 7 lbs with lamp

Electrical

- 1. Dimming:** All configurations are dependent on LED Lamps.
- 2. Photometrics:** Dependant on type of lamp used. Check lamp's spec sheet for details. For additional lamp photometric files, please view the 3D Printed Tailored Lighting configurator website (linked below).
- 3. Wattage:** 145W for 20,000lm, 165W for 25,000lm for Philips HID replacement lamps
- 4. Input Voltage:** 120V - 277V
- 5. Frequency:** 50/60Hz
- 6. Power Factor:** 0.9

Labels

cULus Listed, 5 year warranty, IP20 & RoHS, & IK05

Buy American Act of 1933 (BAA)

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit www.signify.com/baa to view a current list of BAA-compliant products to confirm this product's current compliance.



Unleash your inner creator

To configure your custom 3D printed luminaire, scan this QR Code with your smartphone's camera or visit us at: <https://www.3dprinted.lighting.lightolier.com/en/us/PM-Series/>



PM Series

3D High Bay (20,000lm & 25,000lm)

Colors



CL Clear




DIFF Diffuse




GYSM Smokey Grey



BKST Satin Black



WHST Satin White



GYST Satin Grey

Dimensions

