



# TL5 Essential HE Super 80

## TL5 Essential 14W/865 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

### Product data

General Information	
Cap base	G5 [ G5]
Life to 50% failures preheat (nom.)	20000 h
LSF Preheat 2000 h Rated	98 %
LSF Preheat 4000 h Rated	97 %
LSF Preheat 6000 h Rated	95 %
LSF Preheat 8000 h Rated	93 %
LSF Preheat 16000 h Rated	70 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Colour code	865 [ CCT of 6,500 K]
Luminous flux (nom.)	1260 lm
Luminous flux (rated) (nom.)	1200 lm
Colour designation	Cool Daylight
Luminous efficacy (@ max. lumen, rated) (nom.)	90 lm/W
Correlated colour temperature (nom.)	6500 K
Luminous efficacy (rated) (nom.)	84 lm/W
Color rendering index (max.)	85
Color rendering index (min.)	80
Color rendering index (nom.)	82

LLMF 2000 h Rated	94 %
LLMF 4000 h Rated	92 %
LLMF 6000 h Rated	91 %
LLMF 8000 h Rated	90 %
LLMF 12000 h Rated	88 %
LLMF 16000 h Rated	87 %
LLMF 20000 h Rated	86 %

### Operating and Electrical

Power (Rated) (Nom)	14 W
Lamp current (nom.)	0.170 A

### Temperature

Design temperature (nom.)	30 °C
---------------------------	-------

### Controls and Dimming

Dimmable	No
----------	----

### Approval and Application

Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg

# TL5 Essential HE Super 80


Energy Consumption kWh/1000 h	15 kWh
<b>Product Data</b>	
Full product code	871150057035255
Order product name	TL5 Essential 14W/865 1SL/40
EAN/UPC – product	8711500570352
Order code	57035255

Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927925986558
Net weight (piece)	47.500 g

## Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 14W/865 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

TL5 ESS 14W/865

## Photometric data



Lightcolour /865

## TL5 Essential HE Super 80



أي إقرار أو ضمان فيما يتعلق بدقة أو اكتمال Signify جميع الحقوق محفوظة. لا تقدم شركة Signify Holding حقوق الطبع والنشر 2018 © المعلومات الواردة هنا، ولن تكون مسؤولة عن أي إجراء يعتمد عليه. ولا يُقصد بالمعلومات الواردة في هذه الوثيقة أي عرض تجاري ولا تشكل جزءاً من Koninklijke Philips N.V. هما علامتان تجاريتان مسجلتان لشركة Philips و Philips Shield Emblem أي عرض أو عقد، ما لم يتم الاتفاق على خلاف ذلك. إن Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)

2018, December 10 - data subject to change