



# MASTER PL-S 4 Pin



## MASTER PL-S 11W/830/4P 1CT/5X10BOX

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	2G7	Power Consumption	11.9 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.160 A
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	900 lm	Approval and Application	
Color Designation	Warm White (WW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.44	Mercury (Hg) Content (Max)	1.4 mg
Chromaticity Coordinate Y (Nom)	0.403	Mercury (Hg) Content (Nom)	1.4 mg
Correlated Color Temperature (Nom)	3000 K	Energy Consumption kWh/1000 h	12 kWh
Luminous Efficacy (rated) (Nom)	82 lm/W	EPREL Registration Number	423600
Color rendering index (CRI)	82		

# MASTER PL-S 4 Pin

Product Data	
Order product name	MASTER PL-S 11W/830/4P 1CT/5X10BOX
Full product name	MASTER PL-S 11W/830/4P 1CT/5X10BOX
Full product code	871150026119970
Order code	927936683011
Material Nr. (12NC)	927936683011


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500261199
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500261212

## Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 11W/830/4P 1CT/ 5X10BOX	28 mm	13 mm	196 mm	214 mm	219.9 mm

## Photometric data




Spectral Power Distribution Colour - MASTER PL-S 11W/830/4P 1CT/5X10BOX

## Lifetime




Life Expectancy Diagram - MASTER PL-S 11W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-S 11W/830/4P 1CT/5X10BOX

# MASTER PL-S 4 Pin

## Lifetime



Lumen Maintenance Diagram - MASTER PL-S 11W/830/4P 1CT/5X10BOX

