



MasterColor CDM-T T6 Elite

MASTERColor CDM-T Elite 70W/930 G12 1CT

The Elite family is at the very top of the MasterColor CDM range, and gives a unique combination of unbeatable light quality and consistent performance over lifetime, while keeping running costs low. MasterColor metal halide lamps deliver consistent white light and higher color rendering than any standard metal halide source for architectural lighting.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information		Arc Length O (Nom)	
Cap-Base	G12	7.15 mm	
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	20,000 hour(s)	Power Consumption	73.2 W
Light Technical		Voltage (Nom)	85 V
Color Code	930 [CCT of 3000K]	Voltage (Nom)	85 V
Color Designation	Warm White (WW)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	0.435	Dimmable	No
Chromaticity Coordinate Y (Nom)	0.396	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Bulb Finish	Clear
Luminous Efficacy (rated) (Nom)	103 lm/W		
Color rendering index (CRI)	90		

MasterColor CDM-T T6 Elite

Bulb Shape	T19
------------	-----

Approval and Application


Mercury (Hg) Content (Nom)	6.6 mg
Energy Consumption kWh/1000 h	80 kWh

Product Data

Order product name	MASTERColor CDM-T Elite 70W/930 G12 1CT
Full product name	MASTERColor CDM-T Elite 70W/930 G12 1CT


Order code	928185305115
Material Nr. (12NC)	928185305115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677409159
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677409154

Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERColor CDM-T Elite 70W/930 G12 1CT	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm

Photometric data





Light Distribution Diagram - MASTERColor CDM-T Elite 70W/930 G12 1CT



Spectral Power Distribution Colour - MASTERColor CDM-T Elite 70W/930 G12 1CT


MasterColor CDM-T T6 Elite

Lifetime



Lumen Maintenance Diagram - MASTERColor CDM-T Elite 70W/930 G12 1CT

Lumen Maintenance Diagram - MASTERColor CDM-T Elite 70W/930 G12 1CT



Life Expectancy Diagram - MASTERColor CDM-T Elite 70W/930 G12 1CT

