

# Classic filament LEDbulbs

## CLA LEDBulb ND 4-40W ST64 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data


General Information		Power Consumption	
Cap-Base	E27 [E27]	Lamp Current (Nom)	33 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	40 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	70 °C
Luminous Flux	470 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	118.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	ST64
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Energy Saving Product	Yes
Input Frequency	50 to 60 Hz		

## Classic filament LEDbulbs

Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	4 kWh
EyeComfort	Yes
<b>Product Data</b>	
Order product name	CLA LEDBulb ND 4-40W ST64 E27 827 CL
Full product name	CLA LEDBulb ND 4-40W ST64 E27 827 CL
Full product code	871869657403400


Order code	929001237302
Material Nr. (12NC)	929001237302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574034
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574041

### Dimensional drawing



Product	D	C
CLA LEDBulb ND 4-40W ST64 E27 827 CL	64 mm	140 mm

### Photometric data



Spectral Power Distribution Colour - CLA LEDBulb ND 4-40W ST64 E27 827 CL

General uniform lighting - CLA LEDBulb ND 4-40W ST64 E27 827 CL

Light Distribution Diagram - CLA LEDBulb ND 4-40W ST64 E27 827 CL

# Classic filament LEDbulbs

## Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 4-40W ST64 E27 827 CL

Lumen Maintenance Diagram - CLA LEDBulb ND 4-40W ST64 E27 827 CL

