



LED Highbay

165HB/LED/740/ND WB DL 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	20,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	121.21 lm/W
Color Consistency	ANSI 4000K
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	165 W
Lamp Current (Nom)	3,650 mA
Wattage Equivalent	400 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	52-58 V
UL Type	Type A - works on ballast

Temperature	
T-Case Maximum (Nom)	185 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Others

Approval and Application	
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	165HB/LED/740/ND WB DL 2/1
Full product name	165HB/LED/740/ND WB DL 2/1
Order code	465625

LED Highbay

Material Nr. (12NC)	929001265004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677465629
Numerator - Packs per outer box	2



EAN/UPC - Case	50046677465624
----------------	----------------

Dimensional drawing




Product	D	C
165HB/LED/740/ND WB DL 2/1	8-1/4 inch	9-11/16 inch

Photometric data



General uniform lighting - 165HB/LED/740/ND WB DL 2/1


Spectral Power Distribution Colour - 165HB/LED/740/ND WB DL 2/1




Light Distribution Diagram - 165HB/LED/740/ND WB DL 2/1

LED Highbay

Lifetime



Lumen Maintenance Diagram - 165HB/LED/740/ND WB DL 2/1



Life Expectancy Diagram - 165HB/LED/740/ND WB DL 2/1

