



A-Shape LED

24A35/LED/865/FR/P/E26E39/ND 4/1FB

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Starting Time (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]	Starting Time (Nom)	1 s
Nominal lifetime	25,000 hour(s)	Warm-up time to 60% light	1 s
Switching Cycle	50,000	Power Factor (Fraction)	0.9
Lighting Technology	LED	Voltage (Nom)	120 V
EU RoHS compliant	Yes	Temperature	
Light Technical		T-Case Maximum (Nom)	85 °C
Color Code	865 [CCT of 6500K]	Controls and Dimming	
Beam Angle (Nom)	150 degree(s)	Dimmable	No
Luminous Flux	3,000 lm	Mechanical and Housing	
Color Designation	Cool Daylight	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	6500 K	Bulb Material	Plastic
Luminous Efficacy (rated) (Nom)	125.00 lm/W	Bulb Shape	A35 [A 35mm]
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h	- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Data	
Operating and Electrical		Order product name	24A35/LED/865/FR/P/E26E39/ND 4/1FB
Line Frequency	60 Hz	Full product name	24A35/LED/865/FR/P/E26E39/ND 4/1FB
Input Frequency	60 Hz	Order code	929001854815
Power Consumption	24 W	Material Nr. (12NC)	929001854815
Lamp Current (Nom)	215 mA		
Wattage Equivalent	200 W		

A-Shape LED

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677479299
Numerator - Packs per outer box	4



EAN/UPC - Case	50046677479294
----------------	----------------

Dimensional drawing




Product	D	C
24A35/LED/865/FR/P/E26E39/ND 4/1FB	110 mm	200 mm

Photometric data



Spectral Power Distribution Colour - 24A35/LED/865/FR/P/E26E39/ND 4/1FB

Light Distribution Diagram - 24A35/LED/865/FR/P/E26E39/ND 4/1FB





CalcLUX Photometrics 4.5 Philips Lighting B.V. Page 1/1

General uniform lighting - 24A35/LED/865/FR/P/E26E39/ND 4/1FB

A-Shape LED

Lifetime



Life Expectancy Diagram - 24A35/LED/865/FR/P/E26E39/ND 4/1FB

Lumen Maintenance Diagram - 24A35/LED/865/FR/P/E26E39/ND 4/1FB

