



# Standard LED bulbs

## LEDBulb 23W E27 6500K W A115 1PF/6 BR

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data

<b>General Information</b>		<b>Wattage Equivalent</b>	
Cap-Base	E27 [E27]	180 W	
Nominal lifetime	25,000 hour(s)	<b>Starting Time (Nom)</b>	
Switching Cycle	50,000	1 s	
Lighting Technology	LED	<b>Warm-up time to 60% light</b>	
EU RoHS compliant	Yes	1 s	
<b>Light Technical</b>		<b>Power Factor (Fraction)</b>	
Color Code	865 [CCT of 6500K]	0.7	
Beam Angle (Nom)	150 degree(s)	<b>Voltage (Nom)</b>	
Luminous Flux	3,000 lm	127-220 V	
Color Designation	Cool Daylight	<b>Temperature</b>	
Correlated Color Temperature (Nom)	6500 K	<b>T-Case Maximum (Nom)</b>	
Luminous Efficacy (rated) (Nom)	130.00 lm/W	80 °C	
Color Consistency	<6	<b>Controls and Dimming</b>	
Color rendering index (CRI)	80	<b>Dimmable</b>	
LLMF At End Of Nominal Lifetime (Nom)	70 %	No	
<b>Operating and Electrical</b>		<b>Mechanical and Housing</b>	
Line Frequency	50 to 60 Hz	<b>Bulb Finish</b>	
Input Frequency	50 to 60 Hz	Frosted	
Power Consumption	23 W	<b>Bulb Shape</b>	
		A115 [A 115mm]	
		<b>Approval and Application</b>	
		<b>Energy Consumption kWh/1000 h</b>	
		- kWh	
		<b>Product Data</b>	
		<b>Order product name</b>	
		LEDBulb 23W E27 6500K W A115 1PF/6 BR	
		<b>Full product name</b>	
		LEDBulb 23W E27 6500K W A115 1PF/6 BR	

## Standard LED bulbs



Full product code	871869681575500
Order code	929001863392
Material Nr. (12NC)	929001863392
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696815755

Numerator - Packs per outer box	6
EAN/UPC - Case	8718696815762

## Dimensional drawing

Product	D	C
LEDBulb 23W E27 6500K W A115 1PF/6 BR	115 mm	222 mm

### Photometric data




General uniform lighting - LEDBulb 23W E27 6500K W A115 1PF/6 BR

**Spectral Power Distribution Colour - LEDBulb 23W E27 6500K W A115 1PF/6 BR**

**Light Distribution Diagram - LEDBulb 23W E27 6500K W A115 1PF/6 BR**

Standard LED bulbs

Lifetime



Lumen Maintenance Diagram - LEDBulb 23W E27 6500K W A115 1PF/6 BR

Life Expectancy Diagram - LEDBulb 23W E27 6500K W A115 1PF/6 BR

