



CorePro Plastic (Dimmable) A-Shape Lamps

8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	250 degree(s)
Luminous Flux	800 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz

Input Frequency	
Input Frequency	60 Hz
Power Consumption	8.8 W
Lamp Current (Nom)	80 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19

CorePro Plastic (Dimmable) A-Shape Lamps

UL Wet/ damp/ dry location	Damp location
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT



Full product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT
Order code	929002036204
Material Nr. (12NC)	929002036204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677550448
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677550443

Dimensional drawing



Product	D	C
8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm

Photometric data




Light Distribution Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

General uniform lighting - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT


CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data




Spectral Power Distribution Colour - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Lifetime



Life Expectancy Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT



Lumen Maintenance Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

