



LED Corn Cobs

36CC/LED/830/ND E26 G2 BB 6/1

Philips Corn Cob HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information		Temperature	
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light	1 s
Nominal lifetime	50,000 hour(s)	Power Factor (Fraction)	0.9
Switching Cycle	50,000	Voltage (Nom)	100-277 V
Lighting Technology	LED	UL Type	HIB_UL Type B (UL Listed+Classified)
EU RoHS compliant	Yes	Temperature	
Light Technical		Ambient temperature range	-20 °C to 45 °C
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	60 °C
Luminous Flux	5,000 lm	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	138.00 lm/W	Bulb Finish	Clear
Color Consistency	ANSI 3000K quadrangle	Bulb Material	Plastic
Color rendering index (CRI)	80	Bulb Shape	Corncob
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Energy Consumption kWh/1000 h	36 kWh
Line Frequency	50 to 60 Hz	Application Conditions	
Input Frequency	50 to 60 Hz	can it be used in closed luminaires	Yes
Power Consumption	36 W		
Lamp Current (Nom)	400 mA		
Starting Time (Nom)	1 s		


LED Corn Cobs

Product Data

Order product name	36CC/LED/830/ND E26 G2 BB 6/1
Full product name	36CC/LED/830/ND E26 G2 BB 6/1
Order code	929002395804
Material Nr. (12NC)	929002395804
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	046677559694
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677559699

Dimensional drawing




Product	D	C
36CC/LED/830/ND E26 G2 BB 6/1	85 mm	201 mm

Photometric data



General uniform lighting - 36CC/LED/830/ND E26 G2 BB 6/1


Spectral Power Distribution Colour - 36CC/LED/830/ND E26 G2 BB 6/1



Light Distribution Diagram - 36CC/LED/830/ND E26 G2 BB 6/1

LED Corn Cobs

Lifetime



Life Expectancy Diagram - 36CC/LED/830/ND E26 G2 BB 6/1

Lumen Maintenance Diagram - 36CC/LED/830/ND E26 G2 BB 6/1

