



LED Designer Deco

26UFO/PER/850/FR/P/E26/ND 4/1PF

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Product data

| General Information | |
|---------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |

| Light Technical | |
|---------------------------------------|--------------------|
| Color Code | 850 [CCT of 5000K] |
| Beam Angle (Nom) | 120 degree(s) |
| Luminous Flux | 2,050 lm |
| Color Designation | Daylight |
| Correlated Color Temperature (Nom) | 5000 K |
| Luminous Efficacy (rated) (Nom) | 78.00 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| Operating and Electrical | |
|--------------------------|-------------|
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 26 W |
| Lamp Current (Nom) | 360 mA |
| Wattage Equivalent | 125 W |
| Starting Time (Nom) | 0.5 s |

| | |
|---------------------------|-----------|
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.5 |
| Voltage (Nom) | 110-240 V |

| Temperature | |
|----------------------|-------|
| T-Case Maximum (Nom) | 72 °C |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |

| Mechanical and Housing | |
|------------------------|---------|
| Bulb Finish | Frosted |
| Bulb Material | Plastic |
| Bulb Shape | Others |


| Approval and Application | |
|-------------------------------|-------|
| Energy Consumption kWh/1000 h | - kWh |

| Product Data | |
|-------------------------------|---------------------------------|
| Order product name | 26UFO/PER/850/FR/P/E26/ND 4/1PF |
| Full product name | 26UFO/PER/850/FR/P/E26/ND 4/1PF |
| Order code | 929002441203 |
| Material Nr. (12NC) | 929002441203 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677561642 |

LED Designer Deco



| | |
|---------------------------------|----------------|
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 50046677561647 |

Dimensional drawing




| Product | D | C |
|---------------------------------|--------|-------|
| 26UFO/PER/850/FR/P/E26/ND 4/1PF | 200 mm | 77 mm |

Photometric data



General uniform lighting - 26UFO/PER/850/FR/P/E26/ND 4/1PF

Spectral Power Distribution Colour - 26UFO/PER/850/FR/P/E26/ND 4/1PF



Light Distribution Diagram - 26UFO/PER/850/FR/P/E26/ND 4/1PF

LED Designer Deco

Lifetime



Life Expectancy Diagram - 26UFO/PER/850/FR/P/E26/ND 4/1PF

Lumen Maintenance Diagram - 26UFO/PER/850/FR/P/E26/ND 4/1PF

