



MASTER PL-L 4 Pin

MASTER PL-L 18W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	2G11 [2G11]		82
Nominal lifetime	15,000 hour(s)	Operating and Electrical	
Life to 50% Failures (Nom)	15,000 hour(s)	Power Consumption	18.0 W
		Lamp Current (Nom)	0.375 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	1,200 lm	Approval and Application	
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	2.0 mg
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	67 lm/W		

MASTER PL-L 4 Pin

Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	MASTER PL-L 18W/840/4P 1CT/25
Full product name	MASTER PL-L 18W/840/4P 1CT/25
Full product code	871150070669041
Order code	927903008472


Material Nr. (12NC)	927903008472
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706690
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500610652

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/840/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 18W/840/4P 1CT/25

