



# MASTER PL-C 4 Pin

## 26 W 4 Pin Warm white Non integrated compact fluorescent

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Controls and Dimming	
Cap-Base	G24q-3	Dimmable	Yes
Nominal lifetime	10,000 hour(s)		
Light Technical		Approval and Application	
Color Code	830 [CCT of 3000K]	Mercury (Hg) Content (Nom)	1.4 mg
Luminous Flux	1,800 lm	Energy Consumption kWh/1000 h	29 kWh
Color Designation	Warm White (WW)		
Luminous Efficacy (rated) (Nom)	67 lm/W	Product Data	
Correlated Color Temperature (Nom)	3000 K	Order product name	26 W 4 Pin Warm white Non integrated compact fluorescent
Color rendering index (CRI)	82	Full product name	26 W 4 Pin Warm white Non integrated compact fluorescent
Operating and Electrical		Full product code	871150062335500
Power Consumption	26.0 W	Order code	927907383001
Lamp Current (Nom)	0.335 A	Material Nr. (12NC)	927907383001
		Numerator - Quantity Per Pack	1

# MASTER PL-C 4 Pin

Net Weight (Piece)	60.400 g
EAN/UPC - Product/Case	8711500623355
Numerator - Packs per outer box	50


EAN/UPC - Case	8711500716040
----------------	---------------

## Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
26 W 4 Pin Warm white Non integrated compact fluorescent	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

## Photometric data




Spectral Power Distribution Colour - MASTER PL-C 26W/830/4P 1CT/5X10BOX

## Lifetime



Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

# MASTER PL-C 4 Pin

## Lifetime



Lumen Maintenance Diagram - MASTER PL-C 26W/830/4P 1CT/5X10BOX

