



MASTER TL5 Circular

55 W 2GX13 Cool white T5 Circular fluorescent

16 mm tube diameter circular fluorescent lamps with a choice of various diameters

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2GX13
Nominal lifetime	12,000 h
Flux measurement reference	Sphere
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	4,210 lm
Color Designation	Cool White (CW)
Luminous Efficacy (rated) (Nom)	76 lm/W
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	81
Operating and Electrical	
Power Consumption	55.7 W
Lamp Current (Nom)	0.550 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T5
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	4 mg
Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	56 kWh
EPREL Registration Number	423623
Product Data	
Order product name	55 W 2GX13 Cool white T5 Circular fluorescent
Full product name	55 W 2GX13 Cool white T5 Circular fluorescent
Full product code	871150064251625
Local code description	TL5C55W840
Order code	927965784013
Material Nr. (12NC)	927965784013
Local order code	TL5C55W840

MASTER TL5 Circular

Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.110 kg
EAN/UPC - Product/Case	8711500642516
Numerator - Packs per outer box	10


EAN/UPC - Case	8711500642523
----------------	---------------

Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
55 W 2GX13 Cool white T5	18 mm	14 mm	293 mm	305 mm	260 mm	272 mm
Circular fluorescent						

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 55W/840 1CT/10

Lifetime



Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 55W/840 1CT/10

