



Essential LEDtube

LEDtube 600mm 8W 765 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information		Temperature	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Warm-up time to 60% light	0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)	0.5
Switching Cycle	50,000	Voltage (Nom)	220-240 V
Lighting Technology	LED	Temperature	
EU RoHS compliant	Yes	Ambient temperature range	-20 °C to 45 °C
Light Technical		T-Case Maximum (Nom)	60 °C
Color Code	765 [CCT of 6500K]	Controls and Dimming	
Beam Angle (Nom)	240 degree(s)	Dimmable	No
Luminous Flux	800 lm	Mechanical and Housing	
Color Designation	Cool Daylight	Product Length	600 mm
Correlated Color Temperature (Nom)	6500 K	Bulb Shape	T8
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Approval and Application	
Color Consistency	<7	Energy Saving Product	Yes
Color rendering index (CRI)	73	Suitable For Accent Lighting	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval Marks	RoHS compliance KEMA Keur certificate
Operating and Electrical		Energy Consumption kWh/1000 h	8 kWh
Line Frequency	50 to 60 Hz	Product Data	
Input Frequency	50 to 60 Hz	Order product name	LEDtube 600mm 8W 765 T8 AP I G
Power Consumption	8 W		
Starting Time (Nom)	0.5 s		

Essential LEDtube

Full product name	LEDtube 600mm 8W 765 T8 AP I G
Full product code	871869664605200
Order code	929001184838
Material Nr. (12NC)	929001184838
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	8718696646052
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696646069

Dimensional drawing




Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 765 T8 AP I G	mm		mm	mm	mm	mm	mm

Photometric data



General uniform lighting - LEDtube 600mm 8W 765 T8 AP I G



Light Distribution Diagram - LEDtube 600mm 8W 765 T8 AP I G




Spectral Power Distribution Colour - LEDtube 600mm 8W 765 T8 AP I G

Essential LEDtube


Lifetime




Life Expectancy Diagram - LEDtube 600mm 8W 765 T8 AP I G



Life Expectancy Diagram - LEDtube 600mm 8W 765 T8 AP I G



Life Expectancy Diagram - LEDtube 600mm 8W 765 T8 AP I G



Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP I G

Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP I G

Essential LEDtube

