



LEDLamps

LEDStick 9.5W E27 3000K 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost


Product data

General Information		Wattage Equivalent	
Cap-Base	E27		68 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)	0.51
Lighting Technology	LED	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	Ambient temperature range	-20 to +45 °C
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	85 °C
Beam Angle (Nom)	200 degree(s)	Controls and Dimming	
Luminous Flux	950 lm	Dimmable	No
Luminous Efficacy (rated) (Nom)	100 lm/W	Mechanical and Housing	
Color Designation	White (WH)	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	3000 K	Bulb Material	Plastic
Color Consistency	<6	Bulb Shape	Stick
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	10 kWh
Operating and Electrical		EU RoHS compliant	Yes
Input Frequency	50 to 60 Hz	EyeComfort	Yes
Power Consumption	9.5 W		
Lamp Current (Nom)	75 mA		

LED Innovations	EyeComfort
Product Data	
Order product name	LEDStick 9.5W E27 3000K 1PF/6 AU
Full product name	LEDStick 9.5W E27 3000K 1PF/6 AU
Full product code	871869960527800
Order code	929001901469
Material Nr. (12NC)	929001901469


Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.042 kg
EAN/UPC - Product/Case	8718699605278
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699605285

Dimensional drawing




Product	D	C
LEDStick 9.5W E27 3000K 1PF/6 AU	37.2 mm	114.3 mm


Photometric data



Spectral Power Distribution Colour - LEDStick 9.5W E27 3000K 1PF/6 AU




General uniform lighting - LEDStick 9.5W E27 3000K 1PF/6 AU




Light Distribution Diagram - LEDStick 9.5W E27 3000K 1PF/6 AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDStick 9.5W E27 3000K 1PF/6 AU

