



LED Lamps

LEDStick 9.5W B22 6500K 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data


General Information		Wattage Equivalent	
Cap-Base	B22		75 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)	0.51
Lighting Technology	LED	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	865 [CCT of 6500K]	Ambient temperature range	-20 to +45 °C
Color Code	865 [CCT of 6500K]	T-Case Maximum (Nom)	85 °C
Beam Angle (Nom)	200 degree(s)	Controls and Dimming	
Luminous Flux	1,050 lm	Dimmable	No
Luminous Efficacy (rated) (Nom)	110 lm/W	Mechanical and Housing	
Color Designation	Cool Daylight	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	6500 K	Bulb Material	Plastic
Color Consistency	<6	Bulb Shape	Stick
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	10 kWh
Operating and Electrical		EU RoHS compliant	Yes
Input Frequency	50 to 60 Hz	EyeComfort	Yes
Power Consumption	9.5 W		
Lamp Current (Nom)	84 mA		

LEDLamps

LED Innovations	EyeComfort
Product Data	
Order product name	LEDStick 9.5W B22 6500K 1PF/6 AU
Full product name	LEDStick 9.5W B22 6500K 1PF/6 AU
Full product code	871869960537700
Order code	929001927269
Material Nr. (12NC)	929001927269



Local order code	LSTK9.5WBC865
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.042 kg
EAN/UPC - Product/Case	8718699605377
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699605384

Dimensional drawing




Product	D	C
LEDStick 9.5W B22 6500K 1PF/6 AU	37.2 mm	113 mm

Photometric data



Light Distribution Diagram - LEDStick 9.5W B22 6500K 1PF/6 AU


General uniform lighting - LEDStick 9.5W B22 6500K 1PF/6 AU



Spectral Power Distribution Colour - LEDStick 9.5W B22 6500K 1PF/6 AU

LEDLamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDStick 9.5W B22 6500K 1PF/6 AU

