



LED Lamps

LEDGlobe 7-60W G95 E27 WW 230V_AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Color Code	827 [CCT of 2700K]
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	115 lm/W
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	60 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	45 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	G95


Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
EU RoHS compliant	Yes
EyeComfort	Yes

LEDLamps

LED Innovations	EyeComfort
Product Data	
Order product name	LEDGlobe 7-60W G95 E27 WW 230V_AU
Full product name	LEDGlobe 7-60W G95 E27 WW 230V_AU
Full product code	871869673246500
Local code description	G93806LE27WW
Order code	929002441669
Material Nr. (12NC)	929002441669


Local order code	G93806LE27WW
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.112 kg
EAN/UPC - Product/Case	8718696732465
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514271357

Dimensional drawing




Product	D	C
LEDGlobe 7-60W G95 E27 WW 230V_AU	95 mm	137 mm

Photometric data




Light Distribution Diagram - LEDGlobe 7-60W G95 E27 WW 230V_AU



Spectral Power Distribution Colour - LEDGlobe 7-60W G95 E27 WW 230V_AU

LEDLamps

Photometric data




General uniform lighting - LEDGlobe 7-60W G95 E27 WW 230V_AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDGlobe 7-60W G95 E27 WW 230V_AU

